


METALLURGICAL MICROSCOPE PART NO. 5105-M800



■ Supports observation modes like brightfield, darkfield, polarized light, DIC, etc.

SPECIFICATION

Magnification	50X~1000X						
Eyepiece (wide field)	10X (view field .87"DIA)						
Objective (plan achromatic)	bright & dark field objectives					bright field objectives	
	5X	10X	20X	50X	100X	40X	100X(oil)
Numerical aperture	0.15	0.25	0.40	0.75	0.80	0.65	1.25
Working distance	.47"	.39"	.17"	.01"	.08"	.02"	.01"
Stage	X-Y double layer, size: 7.32×5.43", travel: 2.91×1.97"						
Transmitted illumination light source	24V/100W halogen lamp, brightness is adjustable built-in blue color filter						
Reflected illumination light source	24V/100W halogen lamp, brightness is adjustable built-in green, blue, yellow color filters and frosted glass						
Pupil distance	1.89"~2.95"						
Diopter adjustment	±5 diopter (one eyepiece)						
Power supply	110/220V, 50/60Hz						
Dimension (L×W×H)	25.47×10.55×14.80"						
Weight	39.68lb						

OPTIONAL ACCESSORY

OF HONAL ACCESSORT					
2.5X bright field plan achrom	atic objective	5105-M-OB2.5X			
40X bright and dark field plan achromatic objective		5105-M-BD40X			
DIC objective*	20X	5105-M-DIC20X			
	100X	5105-M-DIC100X			
Rectangular glass stage		5105-M-STAGE			
Polarizer and analyzer		5105-M-POA			
Camera and software**		ISM-MP8B, ISM-KM60,ISM-CM63, ISM-TC80, ISM-MAS100, ISM-MAS200, ISM-MAS300			
0.75X camera adapter		ISM-AD-0D75			
1X camera adapter		ISM-MAS-1XADAPTER			

^{*}DIC objectives must be used with the 5105-M-POA

STANDARD DELIVERY

Main unit	1 pc
Anti-dust cover	1 pc
Blue filter	1 pc

^{**}Camera and software must be used with camera adapter