## PORTABLE REFRACTOMETER

- Quickly measure the concentration of coolant, sugar solution, juice and drinks
- Refer to the refraction factor of coolant, for example: the refraction factor of grinding emulsion is 2.1, the reading value is 6%, so the actual concentration is (2.1×6%)=12.6%

## **SPECIFICATION**

Part No.	ISQ-RM10	ISQ-RM30	ISQ-RM80
Measuring range	0~10%	0~32%	0~80%
Accuracy (20°C)	±0.1%	±0.2%	±0.5%
Resolution	0.1%	0.2%	0.5%
Dimension	1.06×1.57×7.24"	1.06×1.57×6.3"	1.06×1.57×5.39"
Weight	.51lb	.46lb	.41lb



ISQ-RM30